



### HEINE HSL 150® Hand-held Slit Lamp

#### For the examination of the anterior segment



- ∴ Continuous slit adjustment
- ∴ Blue filter
- ∴ Ideal for domiciliary visits

Compact and light-weight, the portable HSL 150 is ideal for situations where a full-size slit lamp is not available or convenient. For the examination of the anterior segment in Human- and Veterinary medicine.

- ∴ **Slit size adjustable** from 0.2 mm x 10 mm to 4 mm x 14 mm.
- ∴ **6x magnification.**
- ∴ **Blue interference filter (FITC)**, can be selected for corneal examination.
- ∴ **Multi-coated optics** for maximum light transmission.
- ∴ **2.5V or 3.5V XHL Xenon Halogen Technology** for bright, white light comparable with the brightness of a classic slit lamp.
- ∴ **The HSL 150 instrument head weighs just 70g**, the lightest slit lamp of its kind.

HSL 150 for BETA or BETA SLIM handles	2.5 V	3.5 V
HSL 150, head only	<b>C-001.14.602</b>	<b>C-002.14.602</b>
XHL Xenon Halogen spare bulb	<b>X-001.88.098</b>	<b>X-002.88.099</b>
Replacement filter attachment for HSL 150		<b>C-000.14.605</b>

### HEINE alpha+ HSL 150® Hand-held Slit Lamp

#### Superior full-size performance in a convenient size



- ∴ Continuous slit adjustment
- ∴ Blue filter
- ∴ Ideal for domiciliary visits

For the examination of the anterior segment in Human- and Veterinary medicine. Basic technical specification similar to HSL 150 (see above), but can only be used with the alpha+ handle system.

alpha+ HSL 150 for alpha+ handles	2.5 V	3.5 V
alpha+ HSL 150, without handle	<b>D-001.81.511</b>	<b>D-002.81.511</b>
<b>alpha+ HSL 150 with alpha+ handle</b>		
alpha+ HSL 150 with alpha+ battery handle	<b>D-302.10.051</b>	
alpha+ HSL 150 with alpha+ rechargeable handle and NT 200 B charger		<b>D-302.20.444</b>
XHL Xenon Halogen spare bulb	<b>X-001.88.098</b>	<b>X-002.88.099</b>
Replacement filter attachment for alpha+ HSL 150		<b>D-000.81.502</b>

### HEINE HSL 10x® Loupe Attachment

#### Loupe attachment with 10x magnification



For HSL 100, 150 and alpha+ HSL 150. With precision magnification optics for crisp, clear images.

- ∴ **10x magnification** when combined with HSL 150 Loupe or alpha+ HSL 150 Loupe.
- ∴ **Increased working distance** from examiner to patient.
- ∴ **Large field of view.**
- ∴ **With an additional detachable TP- elastomer Eyepiece** to steady the instrument on the brow and avoid stray light. Can be replaced with a soft TP- elastomer cap, suitable for spectacle-wearers.

HSL 10x Loupe Attachment	<b>C-000.14.606</b>
--------------------------	---------------------

## HEINE HSL 150® Hand-held Slit Lamp Sets



Set complete with HSL 150 and **BETA SLIM handle** (compact) with:

	2.5 V	3.5 V
BETA SLIM battery handle, in soft pouch, without spare bulb	<b>C-252.10.105</b>	
same, with HSL 10x Loupe Attachment, spare bulb, in hard case	<b>C-268.10.105</b>	
BETA SLIM rechargeable handle and NT 200 charger, spare bulb, in hard case		<b>C-266.20.470</b>
same, with HSL 10x Loupe Attachment, in hard case		<b>C-268.20.470</b>



Set complete with HSL 150, spare bulb and **BETA handle** (standard size),  
in hard case with:

	2.5 V	3.5 V
BETA battery handle	<b>C-265.10.118</b>	
same, with HSL 10x Loupe Attachment	<b>C-267.10.118</b>	
BETA R rechargeable handle		<b>C-265.20.376</b>
same, with HSL 10x Loupe Attachment		<b>C-267.20.376</b>
BETA TR rechargeable handle and transformer		<b>C-265.20.384</b>
same, with HSL 10x Loupe Attachment		<b>C-267.20.384</b>
BETA NT rechargeable handle and NT 200 charger		<b>C-265.20.420</b>
same, with HSL 10x Loupe Attachment		<b>C-267.20.420</b>



Set complete with alpha+ HSL 150 and **alpha+ handle**,  
in hard case with:

	2.5 V	3.5 V
alpha+ battery handle with batteries	<b>D-302.10.051</b>	
same, with HSL 10x Loupe Attachment	<b>D-303.10.051</b>	
alpha+ rechargeable handle and alpha+ NT 200 B charger		<b>D-302.20.444</b>
same, with HSL 10x Loupe Attachment		<b>D-303.20.444</b>

230V is the standard mains voltage. If a different voltage is required,  
e.g. 120V, please specify when ordering.